


Quick Start Guide – TS1000 Turbidity Sensor

Procedures for connecting and configuring the Greenspan TS1000 Sensor. Further details in the Sensor Manual included on the Greenspan CD.


You should have received:

- Certificate of Conformance Sheet
- Greenspan TS1000 Sensor
- Cable Options per order

Sensor fitted with Moulded Cable



Sensor may be fitted with optional Detachable cable



TS1000 provides 2 x calibrated analogue outputs 4-20mA and 0-2.5V over the Sensor Full Scale range. (e.g. 0-100NTU) Sensor requires a nominal 12V DC power supply, but will operate from 8-30V DC